



## Plant Paging/Intercom Station

By Austdac

Catalog # 821-111B100

ICS Outdoor Handset/Speaker Single-party Station, 100-240 VAC, CE Safe area, 8-ohm speaker output, - Orange finish, 6' PVC handset cord



### General

Catalog Number	821-111B100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>• Single Party</li><li>• 8-ohm speaker output</li></ul>
Weather Rating	IP66

### Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in

Weight	13 lb
Width	10.9 in

### Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

### Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

### Product Assets

[Installation Manuals - ICS Weatherproof Page/Party® Handset/Speaker Amplifier Station](#)  
[Literature - ICS Outdoor Stations](#)