



# Plant Paging/Intercom Station

By Austdac  
Catalog # 821-111D204

ICS Offshore Handset/Speaker Single-party Station, 100-240 VAC, UL Class I, Div. 2, 8-ohm speaker output, Stainless steel terminal box, Gray finish, 6' PVC handset cord



## General

Catalog Number	821-111D204
Color	Gray
Material	GRP / Steel / Stainless steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"><li>Offshore Stations</li><li>8-ohm speaker output</li></ul>
Weather Rating	NEMA Type 4X

## Dimensions

Cubic Capacity	3774.246 cu.in
Depth	10.5 in
Height	29.2 in

Weight	30 lb
Width	12.31 in

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

[Installation Manuals - ICS Off-Shore Page/Party® Station](#)  
[Literature - ICS Offshore Stations](#)