

Plant Paging/Intercom Station

By Austdac
Catalog # 821-151D100

ICS SmartSeries Handset/Speaker Single-party Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with Smart Volume - SmartSeries features with RTU input/output - Orange finish, 6' PVC handset cord



Features

Industrial Communication System

General

Catalog Number	821-151D100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Type	<ul style="list-style-type: none"> • Single Party • 8-ohm speaker output with Smart Volume
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
----------------	---------------

Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
[Literature - ICS Outdoor Stations](#)
[Specifications - 821-151D100](#)