

Plant Paging/Intercom Station

By Austdac
Catalog # 821-211B100

ICS Outdoor Handset/Speaker Single-party Station - 100-240VAC - CE Safe area - 8-ohm speaker output - Headset jack - Orange finish, 6' PVC handset cord



Features

Industrial Communication System

General

Catalog Number	821-211B100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	<ul style="list-style-type: none"> • Single Party • 8-ohm speaker output • Headset Jack
Weather Rating	IP66

Dimensions

Cubic Capacity	1670.97 cu.in
----------------	---------------

Depth	10.5 in
Height	14.6 in
Weight	13 lb
Width	10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	CE
Hazardous Rating(s)	CE Safe Area

Product Assets

[Installation Manuals - ICS Weatherproof Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Outdoor Stations](#)
[Specifications - 821-211B100](#)