



# Plant Paging/Intercom Station

By Austdac  
Catalog # 825-121D100

ICS Outdoor Handset/Speaker Multi-party Station - 100-240VAC  
- UL Class I, Div. 2 - 8-ohm speaker output with VLC - Orange  
finish, 6' PVC handset cord



## General

Catalog Number	825-121D100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	NEMA Type 4X

## Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb

Width 10.9 in

## Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

## Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

## Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof  
Page/Party® Station](#)  
[Literature - ICS Outdoor Stations](#)