



Plant Paging/Intercom Station

By Austdac

Catalog # [825-125D2A0](#)

ICS Outdoor Handset/Speaker Multi-party Station - 100-240VAC
- UL Class I, Div. 2 - 8-ohm speaker output with VLC - Gray finish,
15' Hytrel handset cord, PCBA tropicalization



General

Catalog Number	825-125D2A0
Color	Gray
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb

Width 10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof
Page/Party® Station](#)
[Literature - ICS Outdoor Stations](#)