

Plant Paging/Intercom Station

By Austdac
 Catalog # 825-154D1A0

ICS SmartSeries Outdoor Handset/Speaker Multi-party Station - 100-240VAC - UL Class I, Div. 2 - 8-ohm speaker output with SmartVolume - SmartSeries features with RTU input/output - Orange finish, 6' Hytrel handset cord, PCBA tropicalization



Features

Industrial Communication System

General

Catalog Number	825-154D1A0
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in

Weight	13 lb
Width	10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

- [Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
- [Literature - ICS Outdoor Stations](#)
- [Specifications - 825-154D1A0](#)