



Plant Paging/Intercom Station

By Austdac
Catalog # 825-541D100

ICS SmartSeries Outdoor Handset/Speaker Multi-party Station - 24VDC - UL Class I, Div. 2 - 8-ohm speaker output with SmartVolume - SmartSeries features - Orange finish, 6' PVC handset cord



General

Catalog Number	825-541D100
Color	Orange
Material	GRP / Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS SmartSeries
Signal Type	Analog
Weather Rating	NEMA Type 4X

Dimensions

Cubic Capacity	1670.97 cu.in
Depth	10.5 in
Height	14.6 in
Weight	13 lb

Width 10.9 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Div 2

Product Assets

[Installation Manuals - ICS Class I, Div. 2 Weatherproof Page/Party® Station](#)
[Literature - ICS Outdoor Stations](#)