



Plant Paging/Intercom Station

By Austdac

Catalog # 830-810A100

ICS Remote Handset/Speaker Amplifier Station, 24 VDC, 8-ohm speaker output, Orange finish, UL Safe area



General

Catalog Number	830-810A100
Color	Orange
Material	Steel
Output Level Speaker	8 Ohm
Power	30 W
Series	ICS
Signal Type	Analog
Type	Remote Handset/Speaker Amplifier Station
Weather Rating	NEMA Type 12

Dimensions

Cubic Capacity	985.6491 cu.in
Depth	8.18 in
Height	14.5 in

Weight	11 lb
Width	8.31 in

Electrical Ratings

Input Voltage	100-240 VAC
Signal	33 Ohm
Voltage Rating	100-240 VAC

Certifications And Compliance

Certified Listed	UL
Hazardous Rating(s)	UL Safe Area

Product Assets

[Installation Manuals - ICS Remote Subset Page/Party® Handset/Speaker Amplifier Station](#)
[Literature - ICS Remote Stations](#)