



# Analog UL Class I Div 1 Telephone

By Austdac Pty Ltd  
Catalog # 352-001

GAI-Tronics introduces the world's first UL Class I Division 1 telephone and is available in standard analog. This rugged analog handset is UL approved to Class I Division 1 Groups B, C, & D, Class II Groups F & G and Class III, Type 4X, and ABS Type Approved. Analog variants are available with relay contact. Ring relay contacts are 5A, 250 V ac / 30 V dc rated.



## General

Color	Gray
Connectivity Options	Analog
Mount location	Surface-Mount
Output Level Ringer	External required
Signal Type	Analog
Weather Rating	Type 4X

## Dimensions

Cubic Capacity	1175.265 cu.in
Depth	9.36
Height	12.25 in
Weight	28 lb
Width	10.25 in

## Electrical Ratings

Signal	Phone Line
--------	------------

## Certifications and Compliance

Certification	<ul style="list-style-type: none"><li>• UL</li><li>• cUL</li></ul>
Compliance	Telecoms Compliance to Standards: FCC CFR 47 Part 15
Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Division 1, Groups B, C, &amp; D</li><li>• Class II, Division 1, Groups F &amp; G</li><li>• Class III, Division 1</li></ul>

## Product Assets

[Brochures - Rugged Telephone Brochure](#)

[Installation Manuals - Division 1 Telephones \(Model 352-001, 352-002, 352-003, and 352-004\)](#)

[Literature - UL Class I Division 1 Telephones \(VoIP / SMART / Analog\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
AUST\_352-001\_SPEC | REV 3/2023