



## B1412065CHFTC

by Wiegmann  
Catalog ID: B1412065CHFTC

N12 JIC Continuous Hinge - Flanged Trough Collar 14X12X6.5 Carbon Steel - Gray

Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides protection from dust, dirt, oil, and water.

- Bodies and doors fabricated from 14 gauge steel. Special 360° tub flange design diverts contaminants away from tub opening. Continuous hinge. Continuously welded seams ground smooth, less knockouts or holes. Poured-in-place polyurethane gasket. External mounting plates, top and bottom of enclosure. Weldnuts provided for mounting optional panels. With special quick release latches. Grounding provisions provided.

## Product Details

### General

Application	FTC (flange trough collar) enclosures offer unique tub flanges that maximize internal protection. Designed to provide protection from dust, dirt, oil and water.
Color	Gray
Construction	Continuously Welded Seams
Cover Type	Hinged Cover
Finish Type	Textured
Latches Type	Quick-Release Latches
Listings	UL, CSA
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725867288

### Dimensions

Actual Depth	6.54 in
Depth	7 in
Height	14 in
Weight	16 lb
Width	12 in

## Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 12
UL Listed	Yes