

BAF-4824

by CMC
Catalog ID: BAF-4824



Slim line under arm braces, Corrosion resistant 6061-T6 aluminum fittings, Span inches : 48 in, Drop inches : 24 in, Pole mounting hole : 11/16 in, Cross arm mounting hole : 9/16 in

- Lightweight alternative to steel cross braces
- Corrosion resistant 6061-T6 aluminum fittings
- Tongue and groove configuration permanently pins end fitting to wood
- Preservative treated, extra strong Apitong wood resists insect, fungus and environmental attack
- Fittings are press-fit into the wood brace,eliminating the need for static-producing bolted ends. The added strength of the end fitting allows the use of smaller wood members, thereby reducing weight and producing a more eye-pleasing brace that is much stronger than one with bolted fittings
- Reversible style eliminates need for left/right-hand braces
- Sold in pairs

Product Details

General

UPC	192663129577
-----	--------------

Dimensions

Weight	3.260 lb
--------	----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Recognized	No
RUS Listed Reference	Yes



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

