



BASE153030SP

by CMC

Catalog ID: BASE153030SP

Provide a safe and convenient primary cable terminating, sectionalizing, tapping, and switching point for underground distribution systems. Available in sizes for use on single and three phase.

- Constructed of .090 aluminum as standard, .125 available upon request add suffix “-H”
- Single or three phase
- Stainless steel Penta-head bolt and stainless steel padlocking handle
- All 304 stainless steel hardware
- Ground lugs located on mounting plate and on the enclosure for concentric neutral
- Mounting plates are available to fit 2, 3, or 4 way multi-taps with parking stand
- Aluminum, steel or fiberglass burial sleeves available
- A wind stop is included on all top hinged units for operating safety

Product Details

General

Material	Aluminum
UPC	192663132683

Dimensions

Cubic Capacity	13500 cu.in
Depth	15 in
Height	30 in
Width	30 in