



Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, White

By Bell
Catalog # 5197-1



Round Weatherproof Cluster Cover, Three 1/2 in. Threaded Outlets, White

Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Three hole covers supplied with two closure plugs
- NEMA 3R rated

General

Catalog Number	5197-1
Color	White
Construction	Metallic
Cover Type	Lampholder/Cluster
EU RoHS Indicator	Yes
Material	Die Cast Aluminum
Number Of Outlets	3
Type	Cover
UPC	050169519714

Dimensions

Actual Depth	1.094 in
Height	4.125 in

Weight	0.198 lb
Width	4.125 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

Logistics

Carton Quantity	20
Packaging Type	Shrink
Standard Package	20

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - 5193 series, 5197 series](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)