



2-Gang Weatherproof Box, Three 1/2 in. Threaded Outlets, Gray

By Bell
Catalog # 5333-0



2-Gang Weatherproof Box, Three 1/2 in. Threaded Outlets, Gray

Features

- Rugged die-cast aluminum construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Includes two 1/2 in. closure plugs
- Internal hub threads comply with NEMA requirements and will accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package

Specifications

Certified Listed	<ul style="list-style-type: none"> • UL Listed • CSA Certified
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Nema Rating	NEMA 3R
Buy America(n) Qualified	Contact Manufacturer

Configuration

Number of Gang(s)	2-Gang
Number Of Outlets	3

Dimensions

Package Length	2.25 in
Cubic Capacity	32.0 cu.in

Package Width	4.5 in
Package Weight	0.917 lb.
Depth	2.25 in
Package Height	4.5 in
Actual Depth	2.25 in
Thread Size	1/2 in
Width	4.5 in
Height	4.5 in

General

Material type	Metallic
Color	Gray
Construction	Metallic
Type	2-Gang
Material	Aluminum
UPC	050169533307

Logistics

Packaging Type	Shrinkwrap
Standard Package	12
Carton Quantity	12
Pallet Quantity	864

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)