



2-Gang Weatherproof Box, Seven 1/2 in. Threaded Outlets, Gray

By Bell
Catalog # 5338-0

2-Gang Weatherproof Box, Seven 1/2 in. Threaded Outlets, Gray



Features

- Rugged die-cast aluminum construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Eight box mounting options with detachable lugs
- Includes two 1/2 in. closure plugs
- Internal hub threads comply with NEMA requirements and will accept all threaded fittings and threaded conduit
- Ground screw installed
- Multi-lingual instructions in each package

General

Catalog Number	5338-0
Color	Gray
Construction	Metallic
EU RoHS Indicator	Yes
Material	Aluminum
Number Of Outlets	7
Number of Gang(s)	2-Gang
Thread Size	1/2 in
Type	2-Gang
UPC	050169533802

Dimensions

Actual Depth	2.25 in
Cubic Capacity	31 cu.in

Depth	2 in
Height	4.5 in
Weight	1.006 lb
Width	4.5 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
Nema Rating	NEMA 3R

Logistics

Carton Quantity	12
Packaging Type	Shrink
Standard Package	12

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Certifications - UL COC - E195978-3](#)
- [Certifications - UL COC - E195978-2](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 53380 Customer Drawing](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)