



Round Weatherproof Extension Adapter, Four 1/2 in. Threaded Outlets, Gray

By Bell
Catalog # 5363-0



Round Weatherproof Extension Adapter, Four 1/2 in. Threaded Outlets, Gray

Features

- Reinforced connector outlets.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Rugged die cast constructions.
- Four closure plugs included.
- Hubs accept all threaded fittings and threaded conduit.
- Multi-lingual instructions in each package.
- Includes gasket and mounting hardware.
- Rugged die cast aluminum construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance
- Reinforced connector outlets
- Four 1/2 in. closure plugs, installation hardware, and gasket included
- 16.3 cu. in. capacity, 4-1/2 in. outlets

Application

Accessory

Specifications

Certified Listed	<ul style="list-style-type: none"> • UL Listed • CSA Certified
Buy American Compliant	Contact Manufacturer
EU RoHS Indicator	Yes
Nema Rating	NEMA 3R
Buy America(n) Qualified	Contact Manufacturer

Configuration

Number Of Outlets	4
-------------------	---

Dimensions

Package Length	1.625 in
Cubic Capacity	16.3 cu.in
Package Width	4.203 in
Package Weight	0.58 lb.
Depth	1.625 in
Package Height	4.203 in
Actual Depth	1.625 in
Thread Size	1/2 in
Width	4.203 in
Height	4.203 in

General

Material type	Metallic
Color	Gray
Construction	Metallic
Type	Extension/Adapter
Material	Aluminum
UPC	050169536308

Logistics

Packaging Type	Shrinkwrap
Standard Package	16
Carton Quantity	16
Pallet Quantity	1440

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)