



Weatherproof Lampholder, 75-150W Par 38 Lamps, Gray

By Bell
Catalog # 5606-0



Weatherproof Lampholder, 75-150W Par 38 Lamps, Gray

Features

- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Extra-long wire leads and 1/2 lock nut for easy hook up
- Porcelain socket
- Inside Gasket
- Rugged die cast construction
- Multi-lingual instructions in each package

General

Adjustable Detection Sensitivity	No
Catalog Number	5606-0
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Material	Die Cast Aluminum
Type	Lighting
UPC	050169560600
Weather Resistant	Yes

Dimensions

Dimensions	5 in x 2.094 in x 2.094 in
Height	2.094 in
Length	5 in
Range of Motion	180 °
Weight	0.387 lb
Width	2.094 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified Industry Standard(s)	No UL 1598

Logistics

Carton Quantity	30
Packaging Type	Shrink
Standard Package	30

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5606 series, 5612-0](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)