



Weatherproof Lampholder, 75-150W Par 38 Lamps, White

By Bell
Catalog # 5606-1



Weatherproof Lampholder, 75-150W Par 38 Lamps, White

Features

-
-
-
-
-
-
-
-
-
-
-
-
-
-
-

General

Adjustable Detection Sensitivity	No
Catalog Number	5606-1
Color	White
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Material	Die Cast Aluminum
Type	Lighting
UPC	050169560617
Weather Resistant	Yes

Dimensions

Detection Range (ft.)	75 ft
Dimensions	5 in x 2.094 in x 2.094 in
Height	2.094 in
Length	5 in
Range of Motion	110 °
Weight	0.34 lb
Width	2.094 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified	No
Industry Standard(s)	UL 1598

Logistics

Carton Quantity	30
Packaging Type	Shrink
Pallet Quantity	4500
Standard Package	30

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5606 series, 5612-0](#)
- [SDS - HCC SDS](#)
- [Specifications - 5606-1](#)
- [Terms and Conditions - HCC Terms & Conditions](#)