



Weatherproof Lampholder with Gasket, 75-150W Par 38 Lamps, Gray

By Bell
Catalog # 5612-0



Weatherproof Lampholder with Gasket, 75-150W Par 38 Lamps, Gray

Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Extra long wire leads for easy hook-up
- Porcelain socket
- Inside Gasket
- Multi-lingual instructions in each package
- 1/2 in. locknut
- Rugged die-cast construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance
- Use 75 to 150-Watt PAR 38 lamps
- Lamp holders are supplied with extra long wire leads for easy hook up, porcelain sockets, an inside and outside gasket and a 1/2 in. locknut

General

Adjustable Detection Sensitivity	No
Catalog Number	5612-0
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Material	Die Cast Aluminum

Type	Lighting
UPC	050169561201
Weather Resistant	Yes

Dimensions

Dimensions	5 in x 2.5 in x 2.5 in
Height	2.5 in
Length	5 in
Range of Motion	150 °
Weight	0.486 lb
Width	2.5 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified Industry Standard(s)	No UL 1598

Logistics

Carton Quantity	30
Packaging Type	Shrink
Standard Package	30

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5606 series, 5612-0](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)