



Weatherproof Architectural Lampholder, 75-150W Par 38 Lamps, Gray

By Bell
Catalog # 5613-0



Weatherproof Architectural Lampholder, 75-150W Par 38 Lamps, Gray

Features

- Rugged die cast constructions.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming.
- Extra long wire leads for easy hook-up.
- Porcelain socket.
- Inside Gasket.
- Multi-lingual instructions in each package.
- 1/2 in. locknut.
- Premium powder coat finish provides maximum weatherability and scratch resistance
- Rugged die cast construction
- Extra long wire leads
- Porcelain sockets
- Locking Swivel knuckle

General

Adjustable Detection Sensitivity	No
Catalog Number	5613-0
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38

Material	Die Cast Aluminum
Type	Lighting
UPC	050169561300
Weather Resistant	Yes

Dimensions

Dimensions	4.719 in x 2.094 in x 2.094 in
Height	2.094 in
Length	4.719 in
Weight	1.01 lb
Width	2.094 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified Industry Standard(s)	No UL 1598

Logistics

Carton Quantity	4
Packaging Type	Shrink
Standard Package	4

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Sales Drawings - 5613 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)