



# Weatherproof Architectural Lampholder, 75-150W Par 38 Lamps, Bronze

By Bell  
Catalog # 5613-2



Weatherproof Architectural Lampholder, 75-150W Par 38 Lamps, Bronze

## Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Extra long wire leads for easy hook-up
- Porcelain socket
- Inside Gasket
- Multi-lingual instructions in each package
- 1/2 in. locknut
- Rugged die-cast construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance
- Use 75 to 150-Watt PAR 38 lamps
- Lamp holders are supplied with extra long wire leads for easy hook up, porcelain sockets, an inside gasket and a 1/2 in. locknut

## General

Adjustable Detection	No
Sensitivity	
Catalog Number	5613-2
Color	Bronze
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> <li>• Incandescent</li> <li>• PAR 38</li> </ul>

Material	Die Cast Aluminum
Type	Lighting
UPC	050169561324
Weather Resistant	Yes

## Dimensions

Dimensions	4.719 in x 2.094 in x 2.094 in
Height	2.094 in
Length	4.719 in
Range of Motion	150 °
Weight	1.01 lb
Width	2.094 in

## Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> <li>• UL Listed</li> <li>• CSA Certified</li> </ul>
ENERGY STAR Certified Industry Standard(s)	No UL 1598

## Logistics

Carton Quantity	4
Packaging Type	Shrink
Standard Package	4

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Sales Drawings - 5613 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)