



# Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 1 Lampholder, Gasket, and Hardware, Gray

By Bell  
Catalog # 5620-0



Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 1 Lampholder, Gasket, and Hardware, Gray

## Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components
- Premium powder coat finish provides maximum weather ability and scratch resistance
- Rugged die cast construction
- Extra long wire leads
- Porcelain sockets
- Locking swivel knuckle

## General

Adjustable Detection Sensitivity	No
Catalog Number	5620-0
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> <li>• Incandescent</li> <li>• PAR 38</li> </ul>
Material	Die Cast Aluminum
Number Of Outlets	1
Type	<ul style="list-style-type: none"> <li>• Cover</li> </ul>

UPC	• Lighting 050169562000
Weather Resistant	Yes

## Dimensions

Dimensions	5 in x 2.844 in x 4.594 in
Height	4.594 in
Length	5 in
Weight	0.74 lb
Width	2.844 in

## Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer
	<ul style="list-style-type: none"> <li>• UL Listed</li> <li>• CSA Certified</li> </ul>
ENERGY STAR Certified	No

## Logistics

Carton Quantity	8
Packaging Type	Shrink
Standard Package	8

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5620 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)