



Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 1 Lampholder, Gasket, and Hardware, Gray. Carded

By Bell
Catalog # 5620-5

Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 1 Lampholder, Gasket, and Hardware, Gray, Carded



Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components
- Premium powder coat finish provides maximum weather ability and scratch resistance
- Rugged die cast construction
- Extra long wire leads
- Porcelain sockets
- Locking swivel knuckle

General

Adjustable Detection Sensitivity	No
Catalog Number	5620-5
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Number Of Outlets	1
Type	<ul style="list-style-type: none"> • Cover

UPC
Weather Resistant

• Lighting
050169995563
Yes

Dimensions

Dimensions	4.61 in x 2.85 in x 1.07 in
Height	1.07 in
Length	4.61 in
Weight	0.486 lb
Width	2.85 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer
	<ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified	No

Logistics

Carton Quantity	4
Packaging Type	Shrink
Standard Package	8

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5620 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)