



Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, Gray

By Bell
Catalog # 5621-0



Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, Gray

Features

-
-
-
-
-
-

General

Adjustable Detection Sensitivity	No
Catalog Number	5621-0
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Material	Die Cast Aluminum
Number Of Outlets	3
Type	<ul style="list-style-type: none"> • Cover • Lighting
UPC	050169562109
Weather Resistant	Yes

Dimensions

Dimensions	3.336 in x 10 in x 4.594 in
Height	4.594 in
Length	3.336 in
Weight	1.2 lb
Width	10 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified	No

Logistics

Carton Quantity	8
Packaging Type	Shrink
Pallet Quantity	840
Standard Package	8

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5621 series](#)
- [SDS - HCC SDS](#)
- [Specifications - 5621-0](#)
- [Terms and Conditions - HCC Terms & Conditions](#)