



Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, White, Carded

By Bell
Catalog # 5621-6

Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, White, Carded



Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No need to purchase separate components

General

Catalog Number	5621-6
Color	White
Construction	Metallic
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none">• Incandescent• PAR 38
Material	Die Cast Aluminum
Number Of Outlets	3
Type	<ul style="list-style-type: none">• Cover• Lighting
UPC	050169562161

Dimensions

Dimensions	3.336 in x 10 in x 4.594 in
Height	4.594 in
Length	3.336 in
Weight	1.24 lb
Width	10 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
---	--

Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5621 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)