



Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, Bronze, Carded

By Bell

Catalog # 5621-7

Rectangular Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, Bronze, Carded



Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No need to purchase separate components

General

Catalog Number	5621-7
Color	Bronze
Construction	Metallic
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none">• Incandescent• PAR 38
Number Of Outlets	3
Type	<ul style="list-style-type: none">• Cover• Lighting
UPC	050169995570

Dimensions

Dimensions	4.61 in x 2.85 in x 1.07 in
Height	1.07 in
Length	4.61 in
Weight	0.83 lb
Width	2.85 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none">• UL Listed• CSA Certified
-----------------------------------------	----------------------------------------------------------------------------------------------------------

Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - 5621 series](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)