



4 in. Round Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 1 Lampholder, Gasket, and Hardware, Gray, Carded

By Bell
Catalog # 5624-5

4 in. Round Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 1 Lampholder, Gasket, and Hardware, Gray, Carded

Features

- Rugged die cast constructions.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming.
- Includes gasket and mounting hardware.
- Multi-lingual instructions in each package.
- No Need to purchase separate components.

General

Catalog Number	5624-5
Color	Gray
Construction	Metallic
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Material	Die Cast Aluminum
Number Of Outlets	1
Type	<ul style="list-style-type: none"> • Cover • Lighting
UPC	050169562451

Dimensions



Dimensions	3.336 in x 4.125 in x 4.125 in
Height	4.125 in
Length	3.336 in
Weight	0.84 lb
Width	4.125 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
---	---

Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5624 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)