



4 in. Round Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, Bronze

By Bell
Catalog # 5625-2

4 in. Round Weatherproof Combination Cover for 75-150W Par 38 Lamps, Includes 2 Lampholders, Gasket, and Hardware, Bronze

Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components
- Consists of a 4 in. round cover and 2 lamp holders
- Durably die-cast from aluminum and finished in bronze
- Rugged powder-coat finish for scratch resistance
- Wall-mount design

General

Adjustable Detection Sensitivity	No
Catalog Number	5625-2
Color	Bronze
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Material	Die Cast Aluminum
Number Of Outlets	3
Type	<ul style="list-style-type: none"> • Cover • Lighting
UPC	050169562529



Weather Resistant Yes

Dimensions

Detection Range (ft.)	75 ft
Dimensions	3.336 in x 8 in x 4.125 in
Height	4.125 in
Length	3.336 in
Range of Motion	110 °
Weight	0.854 lb
Width	8 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer <ul style="list-style-type: none"> • UL Listed • CSA Certified
ENERGY STAR Certified	No

Logistics

Carton Quantity	8
Packaging Type	Shrink
Standard Package	8

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - 5625 series](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)