



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover, Gray

By Bell
Catalog # 5818-5



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover, Gray

Features

- Rugged die-cast
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Use 75-150 Watt PAR 38 lamps
- Lampholders are supplied with extra long wire leads for easy hook up, porcelain socket, an inside gasket, a 1/2 in. locknut, and the cover is supplied
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No need to purchase separate components

General

Catalog Number	5818-5
Color	Gray
Construction	Metallic
Cover Included	Yes
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Number Of Outlets	3
Toggle Switch	No
Type	<ul style="list-style-type: none"> • Box • Cover

UPC	• Lighting
Weather Resistant	050169581858
	Yes

Dimensions

Dimensions	3.336 in x 10 in x 4.594 in
Height	4.594 in
Length	3.336 in
Weight	1.975 lb
Width	10 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed

Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)