



# Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover, White

By Bell  
Catalog # 5818-6



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover, White

## Features

- Rugged die cast constructions.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming.
- Includes gasket and mounting hardware.
- Multi-lingual instructions in each package.
- No Need to purchase separate components.
- Rugged die cast construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance
- Use 75-150-Watt PAR 38 lamps
- Lampholders are supplied with extra long wire leads for easy hook up, porcelain socket, an inside gasket, a 1/2 in. locknut, and the cover is supplied

## General

Catalog Number	5818-6
Color	White
Construction	Metallic
Cover Included	Yes
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none"> <li>• Incandescent</li> <li>• PAR 38</li> </ul>
Number Of Outlets	3
Toggle Switch	No
Type	<ul style="list-style-type: none"> <li>• Box</li> </ul>

UPC	050169581865
Weather Resistant	Yes

## Dimensions

Dimensions	3.336 in x 10 in x 4.594 in
Height	4.594 in
Length	3.336 in
Weight	1.975 lb
Width	10 in

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed

## Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)