



Outdoor Light Kit with (2) 150W (max) PAR38 Lampholders, Round Box, and Cover, Gray



By Bell
Catalog # 5829-5G

4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover and External Gasket, Gra

Features

- Premium powder coat finish provides maximum weatherability and scratch resistance.
- Rugged die cast construction.
- Extra long wire leads.
- Porcelain sockets.
- Locking swivel knuckle.
- Use 75-150W PAR 38 lamps.
- Outside gasket.
- 1/2 in. NPT Thread.
- CFL compatible.

General

| | |
|----------------------------------|---------------|
| Adjustable Detection Sensitivity | No |
| Catalog Number | 5829-5G |
| Color | Gray |
| Dusk to Dawn | No |
| Glass/Lens Type | No Glass/Lens |
| Light Source | Incandescent |
| Material | Cast Metal |
| UPC | 050169917190 |
| Weather Resistant | Yes |

Dimensions

| | |
|------------|------------------------------|
| Dimensions | 2.55 in x 4.52 in x 7.875 in |
| Height | 7.875 in |
| Length | 2.55 in |
| Weight | 1.34 lb |
| Width | 4.52 in |

Certifications And Compliance

| | |
|------------------------|----------------------|
| Buy American Compliant | Contact Manufacturer |
| Certified Listed | UL Listed |
| ENERGY STAR Certified | No |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 4 |
| Minimum Pack Quantity | 4 |
| Pallet Quantity | 576 |

Product Assets

- [360 Product View - BELL_5829-5G](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Specifications - 5829-5G](#)
- [Terms and Conditions - HCC Terms & Conditions](#)