



4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover, White



By Bell
Catalog # 5829-6

4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover, White

Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components
- Rugged die cast aluminum construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance and have a white finish
- 2-lampholders for use with 75-150-Watt PAR38 lamps
- Installation hardware, gasket and multilingual instructions included

General

Adjustable Detection Sensitivity	No
Catalog Number	5829-6
Color	White
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Number Of Outlets	3
Type	<ul style="list-style-type: none"> • Box • Cover

UPC	• Lighting 050169582961
Weather Resistant	Yes

Dimensions

Detection Range (ft.)	75 ft
Dimensions	4.961 in x 8 in x 4.125 in
Height	4.125 in
Length	4.961 in
Range of Motion	110 °
Weight	1.75 lb
Width	8 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
ENERGY STAR Certified	No

Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)