



4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover and Photocell, Gray

By Bell
Catalog # 5841-5



4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, and Cover and Photocell, Gray

Features

- Rugged die cast constructions
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- No Need to purchase separate components
- Rugged die cast construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance
- Use 75-150W PAR 38 lamps
- Lampholders are supplied with extra long wire leads for easy hook up, porcelain socket, an inside gasket, and a 1/2 In. locknut
- Cover is supplied with gasket

General

Adjustable Detection Sensitivity	No
Catalog Number	5841-5
Color	Gray
Construction	Metallic
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Number Of Outlets	3
Type	<ul style="list-style-type: none"> • Box • Cover

UPC
Weather Resistant

- Lighting
 - Photocell
- 050169584156
Yes

Dimensions

Detection Range (ft.)	50 ft
Dimensions	2.625 in x 5 in x 8.125 in
Height	8.125 in
Length	2.625 in
Range of Motion	220 °
Weight	1.825 lb
Width	5 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
ENERGY STAR Certified	No

Logistics

Carton Quantity	4
Packaging Type	Carded
Pallet Quantity	240
Standard Package	4

Product Assets

[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)