



# 4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Architectural Lampholders, Box, and Cover, Bronze

By Bell  
Catalog # 5876-7



4 in. Round Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Architectural Lampholders, Box, and Cover, Bronze

## Features

- Rugged die cast constructions.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming.
- Includes gasket and mounting hardware.
- Multi-lingual instructions in each package.
- No Need to purchase separate components.
- Rugged die cast aluminum construction
- State of the art powder coat finish provides maximum weather ability and scratch resistance and have a bronze finish
- 2 lampholders for use Watt 75-150 Watt par 38 lamps
- Installation hardware, gasket and multilingual instructions included
- Note: product may vary by store

## General

Adjustable Detection Sensitivity	No
Catalog Number	5876-7
Color	Bronze
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> <li>• Incandescent</li> <li>• PAR 38</li> </ul>
Number Of Outlets	3

Type	<ul style="list-style-type: none"> <li>• Box</li> <li>• Cover</li> <li>• Lighting</li> </ul>
UPC	050169587676
Weather Resistant	Yes

## Dimensions

Detection Range (ft.)	75 ft
Dimensions	3.336 in x 10 in x 4.594 in
Height	4.594 in
Length	3.336 in
Weight	2.498 lb
Width	10 in

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
ENERGY STAR Certified	No

## Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)