



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, Cover, and Photocell, Gray

By Bell
Catalog # 5883-5



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, Cover, and Photocell, Gray

Features

- Rugged die cast constructions.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming.
- Includes gasket and mounting hardware.
- Multi-lingual instructions in each package.
- No Need to purchase separate components.
- Premium powder coat finish provides maximum weather ability and scratch resistance
- Rugged die cast construction
- Extra long wire leads
- Porcelain sockets
- Locking swivel knuckle

General

Adjustable Detection Sensitivity	No
Catalog Number	5883-5
Color	Gray
Construction	Metallic
Dusk to Dawn	No
EU RoHS Exemption	6b
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Type	<ul style="list-style-type: none"> • Box

- Cover
 - Lighting
 - Photocell
- 050169588352
Yes

UPC
Weather Resistant

Dimensions

Dimensions	2.125 in x 2.75 in x 10.938 in
Height	10.938 in
Length	2.125 in
Weight	1.823 lb
Width	2.75 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
ENERGY STAR Certified	No

Logistics

Carton Quantity	4
Packaging Type	Boxed
Standard Package	4

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)