



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, Cover, and Photocell, White

By Bell
Catalog # 5883-6



Rectangular Light Weatherproof Kit for 75-150W Par38 Lamps, Includes 2-Lampholders, Box, Cover, and Photocell, White

Features

- Rugged die cast constructions.
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance.
- Locking swivel knuckle assures positive lamp positioning and provides pin-point directional aiming.
- Includes gasket and mounting hardware.
- Multi-lingual instructions in each package.
- No Need to purchase separate components.
- Rugged die cast construction
- State of the art powder coat finish provides maximum weatherability and scratch resistance
- Use 75-150 Watt PAR 38 lamps
- Lampholders are supplied with extra long wire leads for easy hook up, porcelain socket, an inside gasket, and a 1/2 in. locknut

General

Catalog Number	5883-6
Color	White
Construction	Metallic
Cover Included	Yes
EU RoHS Indicator	Yes
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none"> • Incandescent • PAR 38
Toggle Switch	No
Type	<ul style="list-style-type: none"> • Box • Cover

UPC
Weather Resistant

- Lighting
- Photocell

050169588369
Yes

Dimensions

Dimensions	2.125 in x 2.75 in x 10.938 in
Height	10.938 in
Length	2.125 in
Weight	1.823 lb
Width	2.75 in

Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer UL Listed
--	-----------------------------------

Logistics

Carton Quantity	4
Packaging Type	Carded
Standard Package	4

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)