



# 4-Tier Incandescent Metallic Garden Light, 1/2 in. NPT and 18 in. leads

By Bell  
Catalog # 5893-8

4-Tier Incandescent Metallic Garden Light, 1/2 in. NPT and 18 in. leads

### Features

- Rugged die cast construction
- State-of-the-art powdercoat finish provides maximum weatherability and scratch-resistance
- Accepts 60 watt maximum lamps
- Includes screw-in clear glass globe, wire connectors, gasket, and multi-lingual instructions

### General

Catalog Number	5893-8
Color	Green
Dusk to Dawn	No
EU RoHS Indicator	Yes
Fixture Type	Landscape
Glass/Lens Type	Clear
Light Source	Incandescent
Lighting Kit	Yes
Material	Metallic
Mounting Type	Ground
Number of Housings Included	1
Type	Lighting
UPC	050169589380
Waterproof	Yes
Weather Resistant	Yes

### Dimensions

Dimensions	5.125 in x 5.625 in x 8.813 in
------------	--------------------------------



Height	8.813 in
Length	5.125 in
Weight	3.48 lb
Width	5.625 in

### Electrical Ratings

Lamp Wattage	60 W
Primary Voltage	120 V
Wattage Range	0-60 W

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
ENERGY STAR Certified	No

### Logistics

Carton Quantity	2
Packaging Type	Box
Standard Package	2

### Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Installation Manuals - Tiered Incandescent Garden Lights](#)
- [Sales Drawings - 5884-8 5893-8](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)