



Weatherproof Swivel Lampholder, Halogen 75W (GY 8.6 TYPE 4), White

By Bell
Catalog # [LHS100W](#)



Weatherproof Swivel Lampholder, Halogen 75W (GY 8.6 TYPE 4), White

Features

- Rugged die cast construction ideal for outdoor installation
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Uses halogen bulb which lasts up to 3 times longer and produces almost 50% more light for the same amount of energy compared to incandescent bulbs
- Innovative no-tool easy-mount feature offers hassle-free installation
- Swivel joint for easy directional lighting
- Mounts on wall to illuminate yards and decks
- Weather-resistant housing protects against damage due to exposure to the elements

General

Adjustable Detection	No
Sensitivity	
Catalog Number	LHS100W
Color	White
Construction	Metallic
Dusk to Dawn	No
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	Clear
Light Source	Halogen
Material	Die Cast Aluminum
Type	Lighting
UPC	092326110280
Weather Resistant	Yes

Dimensions

Dimensions	4 in x 3.7 in x 5.25 in
Height	5.25 in
Length	4 in
Weight	0.567 lb
Width	3.7 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL Listed
ENERGY STAR Certified	No
NEC	Compliant

Logistics

Carton Quantity	6
Packaging Type	Shrink
Pallet Quantity	960
Standard Package	6

Product Assets

[360 Product View - BELL_LHS100W](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - LHS100](#)
[SDS - HCC SDS](#)
[Specifications - LHS100W](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand