



LED Swivel Floodlight, 1200 Lumens, Gray

By Bell
Catalog # LL1200S

LED Swivel Floodlight, 1200 Lumens, Gray



Features

- 85% less energy consumption compared to incandescent bulb with similar light
- Uses only 13W
- 1200 Lumens (equivalent to 75W incandescent) of 3000k warm white light
- Rugged die-cast aluminum heads
- 120/277 VAC 50/60 Hz
- Unique locking swivel joint for easy light adjustment
- Long life - up to 50,000 hours
- 6" lead wires
- Tempered glass lens
- Tool-free mounting to Bell boxes, covers & cluster covers
- DLC Listed

General

Catalog Number	LL1200S
Color	Gray
Color Temperature	3000 K
Color Temperature Description	Warm White
Construction	Metallic
Fixture Type	Architectural;Flood;Swivel
Light Source	LED
Material	Die Cast Aluminum
Type	Lighting
UPC	050169994771
Weather Resistant	Yes

Dimensions

Dimensions	5.051 in x 3.738 in x 4.686 in
Height	4.686 in
Length	5.051 in
Weight	0.815 lb
Width	3.738 in

Electrical Ratings

Lumens Per Watt	97.8
Wattage	12.6 W

Certifications And Compliance

Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	3R

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Standard Package	1

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - LL1200 LED Swivel Floodlight](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - BELL: LL800 & LL1200 Outdoor LED Swivel Floodlight](#)