



LED Swivel Floodlight, 1200 Lumens, Bronze

By Bell
Catalog # LL1200Z

LED Swivel Floodlight, 1200 Lumens, Bronze



Features

- 85% less energy consumption compared to incandescent bulb with similar light
- Uses only 13W
- 1200 Lumens (equivalent to 75W incandescent) of 3000k warm white light
- Rugged die-cast aluminum heads
- 120/277 VAC 50/60 Hz
- Unique locking swivel joint for easy light adjustment
- Long life - up to 50,000 hours
- 6" lead wires
- Tempered glass lens
- Tool-free mounting to Bell boxes, covers & cluster covers
- DLC Listed

General

| | |
|-------------------------------|----------------------------|
| Catalog Number | LL1200Z |
| Color | Bronze |
| Color Temperature | 3000 K |
| Color Temperature Description | Warm White |
| Construction | Metallic |
| Fixture Type | Architectural;Flood;Swivel |
| Light Source | LED |
| Material | Die Cast Aluminum |
| Type | Lighting |
| UPC | 050169994795 |
| Weather Resistant | Yes |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 5.051 in x 3.738 in x 4.686 in |
| Height | 4.686 in |

| | |
|--------|----------|
| Length | 5.051 in |
| Weight | 0.815 lb |
| Width | 3.738 in |

Electrical Ratings

| | |
|-----------------|--------|
| Lumens Per Watt | 97.8 |
| Wattage | 12.6 W |

Certifications And Compliance

| | |
|------------------|--------------|
| Certified Listed | cULus Listed |
| NEC | Compliant |
| Nema Rating | 3R |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 4 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 480 |
| Standard Package | 1 |

Product Assets

- [360 Product View - BELL_LL1200Z](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - LL1200 LED Swivel Floodlight](#)
- [Specifications - LL1200Z](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - BELL: LL800 & LL1200 Outdoor LED Swivel Floodlight](#)