

# LED Swivel Floodlight, 1200 Lumens, Bronze

By Bell Catalog # LL1200Z

LED Swivel Floodlight, 1200 Lumens, Bronze



#### **Features**

- 85% less energy consumption compared to incandescent bulb with similar light
- Uses only 13W
- 1200 Lumens (equivalent to 75W incandescent) of 3000k warm white light
- Rugged die-cast aluminum heads
- 120/277 VAC 50/60 Hz
- · Unique locking swivel joint for easy light adjustment
- Long life up to 50,000 hours
- 6" lead wires
- Tempered glass lens
- Tool-free mounting to Bell boxes, covers & cluster covers
- DLC Listed

# General

Catalog Number LL1200Z
Color Bronze
Color Temperature 3000 K
Color Temperature Description Warm White
Construction Metallic

Fixture Type Architectural;Flood;Swivel

Light Source LED

Material Die Cast Aluminum

Type Lighting UPC 050169994795

Weather Resistant Yes

#### **Dimensions**

Dimensions 5.051 in x 3.738 in x 4.686 in

 Height
 4.686 in

 Length
 5.051 in

 Weight
 0.815 lb

 Width
 3.738 in

### **Electrical Ratings**

Lumens Per Watt 97.8 Wattage 12.6 W

# **Certifications And Compliance**

Certified Listed CULus Listed
NEC Compliant
Nema Rating 3R

## Logistics

Carton Quantity 4
Minimum Pack Quantity 1
Standard Package 1

#### **Product Assets**

Catalogs - RACO / TayMac / Bell Full Catalog

Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50 Customer Notices - Prop 65 - Cancer & Reproductive Harm

Notice

SDS - HCC SDS

Sell Sheets - LL1200 LED Swivel Floodlight Terms and Conditions - HCC Terms & Conditions

Video - BELL: LL800 & LL1200 Outdoor LED Swivel Floodlight