



LED Swivel Floodlight, 800 Lumens, White

By Bell
Catalog # [LL800W](#)

LED Swivel Floodlight, 800 Lumens, White



Features

- 85% less energy consumption compared to incandescent bulb with similar light
- Uses only 8W
- 800 Lumens (equivalent to 60W incandescent) of 3000k warm white light
- Rugged die-cast aluminum heads
- 120VAC 60Hz
- Swivel joint for easy light adjustment
- Long life - up to 50,000 hours
- 6" lead wires
- Tempered glass lens
- Tool-free, easy mounting to Bell boxes, covers & cluster covers

General

Catalog Number	LL800W
Color	White
Color Temperature	3000 K
Color Temperature Description	Warm White
Construction	Metallic
Fixture Type	Architectural;Flood;Swivel
Light Source	LED
Material	Die Cast Aluminum
Type	Lighting

UPC 050169994757
Weather Resistant Yes

Electrical Ratings

Wattage 8 W

Certifications And Compliance

Certified Listed cULus Listed
NEC Compliant
Nema Rating 3R

Logistics

Carton Quantity 4
Minimum Pack Quantity 1
Standard Package 1

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[SDS - HCC SDS](#)
[Sell Sheets - LL800 LED Swivel Floodlight](#)
[Terms and Conditions - HCC Terms & Conditions](#)
[Video - BELL: LL800 & LL1200 Outdoor LED Swivel Floodlight](#)