



LED Swivel Floodlight, 800 Lumens, Bronze

By Bell
Catalog # LL800Z

LED Swivel Floodlight, 800 Lumens, Bronze



Features

- 85% less energy consumption compared to incandescent bulb with similar light
- Uses only 8W
- 800 Lumens (equivalent to 60W incandescent) of 3000k warm white light
- Rugged die-cast aluminum heads
- 120VAC 60Hz
- Swivel joint for easy light adjustment
- Long life - up to 50,000 hours
- 6" lead wires
- Tempered glass lens
- Tool-free, easy mounting to Bell boxes, covers & cluster covers

General

Catalog Number	LL800Z
Color	Bronze
Color Temperature	3000 K
Color Temperature Description	Warm White
Construction	Metallic
Fixture Type	Architectural;Flood;Swivel
Light Source	LED
Material	Die Cast Aluminum
Type	Lighting
UPC	050169994764
Weather Resistant	Yes

Dimensions

Dimensions	4.492 in x 3.966 in x 4.584 in
Height	4.584 in
Length	4.492 in
Weight	0.794 lb
Width	3.966 in

Electrical Ratings

Wattage	8 W
---------	-----

Certifications And Compliance

Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	3R

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Standard Package	1

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - LL800 LED Swivel Floodlight](#)
- [Terms and Conditions - HCC Terms & Conditions](#)
- [Video - BELL: LL800 & LL1200 Outdoor LED Swivel Floodlight](#)