



Weatherproof Swivel Lampholder, Traditional or CFL, Use Par 38 Bulb, Gray

By Bell
Catalog # LTS100S



Weatherproof Swivel Lampholder, Traditional or CFL, Use Par 38 Bulb, Gray

Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes porcelain sockets and external weatherproof gaskets
- Innovative no-tool easy-mount feature
- Swivel joint for easy directional lighting

General

Catalog Number	LTS100S
Color	Gray
Construction	Metallic
EU RoHS Indicator	Contact Manufacturer
Fixture Type	Architectural;Flood;Swivel
Light Source	<ul style="list-style-type: none"> • CFL • PAR 38
Material	Die Cast Aluminum
Type	Lighting
UPC	092326111409
Weather Resistant	Yes

Dimensions

Dimensions	2.6 in x 4 in x 5.56 in
Height	5.56 in
Length	2.6 in
Weight	0.37 lb
Width	4 in

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Sales Drawings - LTS100](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)