



# Weatherproof Lampholder, Nonmetallic, White

By Bell  
Catalog # PLTS100WH

Weatherproof Lampholder, Nonmetallic, White



## Features

- Durable high impact polycarbonate construction
- Porcelain lamp sockets
- No-tool easy-mount feature
- Use 75-150-Watt PAR 38 lamps
- Extra long wire leads
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package

## General

Adjustable Detection Sensitivity	No
Catalog Number	PLTS100WH
Color	White
Construction	Nonmetallic
Dusk to Dawn	No
EU RoHS Indicator	No
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
Light Source	<ul style="list-style-type: none"> <li>• Incandescent</li> <li>• PAR 38</li> </ul>
Type	Lighting
UPC	092326130226
Weather Resistant	Yes

## Dimensions

Dimensions	2.4 in x 4.48 in x 4.78 in
Height	4.78 in
Length	2.4 in
Weight	0.3 lb
Width	4.48 in

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
ENERGY STAR Certified	No
NEC	Compliant
Nema Rating	NEMA 3R

## Logistics

Carton Quantity	12
Packaging Type	Shrink
Standard Package	12

## Product Assets

- [Brochures - Non-metallic Weatherproof Boxes, Covers & Lighting](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Sales Drawings - PLTS100](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)