



## 2-Gang Weatherproof Cover, Plastic, Toggle/Toggle, Gray

By Bell  
Catalog # [PTC200GY](#)

2-Gang Weatherproof Cover, Plastic, Toggle/Toggle, Gray



### Features

- Durable high-impact polycarbonate construction
- Patented horseshoe adapter ensures a snug fit for small and large head switches
- Attached gasket and mounting hardware included
- Vertical mount

### Application

Switch Cover

### General

Catalog Number	PTC200GY
Color	Gray
Construction	Nonmetallic
Cover Type	Toggle
EU RoHS Indicator	Contact Manufacturer
Material	Nonmetallic
Number of Gang(s)	2-Gang
Type	Cover
UPC	092326130110
Weather Resistant	Yes

### Dimensions

Actual Depth	2 in
Height	4.75 in
Weight	0.338 lb

Width 4.88 in

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	UL Listed
NEC	Compliant
Nema Rating	NEMA 3R

### Logistics

Carton Quantity	3
Packaging Type	Shrink
Pallet Quantity	1260
Standard Package	4

### Product Assets

- [Brochures - Non-metallic Weatherproof Boxes, Covers & Lighting](#)
- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Certifications - UL COC-E116141-2](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - PTC200](#)
- [SDS - HCC SDS](#)
- [Specifications - PTC200GY](#)
- [Terms and Conditions - HCC Terms & Conditions](#)