



# Portable Spike Light 500 Lumen LED

By Bell  
Catalog # SPLED500Z

Portable Spike Light 500 Lumen LED



## Features

- Rugged die-cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Multi-directional swivel joint
- Long Life: 50,000 hours

## General

Catalog Number	SPLED500Z
Color	Bronze
Color Temperature	3000 K
Color Temperature Description	Warm White
Construction	Metallic
EU RoHS Indicator	No
Fixture Type	Architectural;Landscape;Portable
Light Output	540 lm
Light Source	LED
Lumens	0-2000 Lumens
Mounting Type	Ground
Type	Lighting
UPC	050169917589
Weather Resistant	Yes

## Dimensions

Dimensions	12.5 in x 4.0 in x 4.0 in
Height	4 in
Length	12.5 in
Weight	1.438 lb

Width 4 in

## Electrical Ratings

Frequency Rating	60 Hz
Lamp Wattage	8.7 W
Lumens Per Watt	62
Voltage Rating	120 V
Wattage	8.7 W

## Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certified Listed	cULus Listed
NEC	Compliant
Nema Rating	NEMA 3R

## Logistics

Carton Quantity 4

## Product Assets

- [Catalogs - RACO / TayMac / Bell Full Catalog](#)
- [Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Sales Drawings - SPLED500Z](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - LED Swivel Joint Spikelight](#)
- [Terms and Conditions - HCC Terms & Conditions](#)