



Round Weatherproof Cluster Cover, One 1/2 in. Threaded Outlets, White

By Bell
Catalog # 5193-1



Round Weatherproof Cluster Cover, One 1/2 in. Threaded Outlets, White.

Features

- Rugged die cast construction
- State-of-the-art powder coat finish provides maximum weatherability and scratch resistance
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package
- Three hole covers supplied with two closure plugs
- No closure plugs included
- NEMA 3R rated

General

Color	<ul style="list-style-type: none">• White• Blanc
Construction	Metallic
Cover Type	Lampholder/Cluster
Material	Die Cast Aluminum
Number Of Outlets	1
Type	<ul style="list-style-type: none">• Cover• Cover
UPC	050169519318

Dimensions

Actual Depth	1.094 in
Height	4.125 in
Weight	0.15 lb
Width	4.125 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL Listed• CSA Certified
Industry Standard(s)	UL 514A
Nema Rating	NEMA 3R

Logistics

Carton Quantity	20
Packaging Type	Shrink
Pallet Quantity	3000
Standard Package	20

Product Assets

[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Sales Drawings - 5193 series, 5197 series](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BELL_CA-5193-1-SPEC-EN | REV 1/2024