



Weatherproof Lampholder, Nonmetallic, White

By Bell
Catalog # [PLTS100WH](#)



Weatherproof Lampholder, Nonmetallic, White

Features

- Durable high impact polycarbonate construction
- Porcelain lamp sockets
- No-tool easy-mount feature
- Use 75-150-Watt PAR 38 lamps
- Extra long wire leads
- Includes gasket and mounting hardware
- Multi-lingual instructions in each package

General

Adjustable Detection	No
Sensitivity	
Catalog Number	PLTS100WH
Construction	Nonmetallic
Dusk to Dawn	No
EU RoHS Indicator	No
Fixture Type	Architectural;Flood;Swivel
Glass/Lens Type	No Glass/Lens
UPC	092326130226
Weather Resistant	Yes

Dimensions

Dimensions	2.4 in x 4.48 in x 4.78 in
Height	4.78 in
Length	2.4 in
Weight	0.3 lb

Width 4.48 in

Certifications And Compliance

Certified Listed	UL Listed
ENERGY STAR Certified	No
NEC	Compliant
Nema Rating	NEMA 3R

Logistics

Carton Quantity	12
Packaging Type	Shrink
Pallet Quantity	1920
Standard Package	12

Product Assets

[360 Product View - BELL_PLTS100WH](#)
[Brochures - Non-metallic Weatherproof Boxes, Covers & Lighting](#)
[Catalogs - RACO / TayMac / Bell Full Catalog](#)
[Catalogs - Weatherproof Boxes, Covers & Lighting D1-D50](#)
[Sales Drawings - PLTS100](#)
[SDS - HCC SDS](#)
[Specifications - PLTS100WH Specification Sheet](#)
[Specifications - PLTS100WH](#)
[Specifications - PLTS100WH Specification Sheet French](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand